

# ALPHA STAINLESS

8470UFD100P30-11

EAN 4031582370096



BETTER MOBILITY. BETTER LIFE.



Slika se može razlikovati od originalnog proizvoda

## PERFORMANSE

Performanse kotrljanja ●●●○○

Buka u pokretu ●●●●●

Ishrana ●●●○○

otpornost na rdju ●●●●●

## OSNOVNI ATRIBUTI

Naziv proizvoda	Alpha stainless
Tip	Okretanje Tocak
Standard	EN12532 - transportna oprema
Nosivost na 4 km/h	150 kg
nerdjajuci	✓
Statički Nosivost	300 kg
Temperaturni opseg (Minimalno)	-20 °C
Opseg temperature (maksimalni)	80 °C
Sveukupna visina	128 mm
Ukupna težina	0,744 kg

## TOCAK

Materijal za telo	poliamid
	mekan
materijal omotaca	Elastična guma, neobeležena, vulkanizovana
Nošenje	kotrljajuci lezaj, nerdjajuci
osovina	Završena sa navrtkom
Prečnik	100 mm
Širina omotac	34 mm
Teškoća gazećeg omotac (A)	64 Šešelj A

## KUCISTE

Materijal	nerdjajuci čelik, težak
oblik viljuska	siroko
okretni lezaj	Dve lopte
ofset	41 mm
okretni radijus	91 mm
Otpor okretanju	182 mm

## PRILAGOĐAVANJE

Tip uklapanja	otvor za vijak
dimenzija rupa sraf	11 mm

# ALPHA STAINLESS

8470UFD100P30-11

EAN 4031582370096



BETTER MOBILITY. BETTER LIFE.

## TEHNIČKI CRTEŽI

