

# ALPHA STAINLESS

8470BOG100P30-13 HT

EAN 4031582373394  
Order number 00061132



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## PERFORMANCE

Roll performance	●●●○○
Movement noise	●●○○○○
Attrition	●●●●●
Corrosion resistance	●●●●●

## CORE ATTRIBUTES

Product name	Alpha stainless
Type	Swivel castor
Standard	EN12532 - Transport Equipment
Load capacity at 2.5 mph	275.58 lb
Stainless	✓
Load capacity Static	551.16 lb
Temperature range (Minimum)	-40 °F
Temperature range (Maximum)	482 °F
Overall height	5.04 in
Overall width	2.95 in
Overall weight	1.5 lb

## WHEEL

Body material	Plastic thermoset, heat-resistant
Tread material	Identical with wheel body
Bearing	Dry bearing bush
Axle	Screwed with nut
Wheel color	Black
Diameter	3.94 in
Tread width	1.38 in
Body width	1.38 in
Hardness of tread (D)	90 Shore D

## HOUSING

Material	Stainless steel, heavy
Fork shape	Broad
Swivel bearing	Two ball races
Color	Stainless steel
Offset	1.61 in
Swivel radius	3.58 in
Swivel interference	7.17 in
Dome diameter	2.95 in

## FITTING

Fitting type	Bolt hole
Bolt hole diameter	0.51 in

# ALPHA STAINLESS

8470BOG100P30-13 HT

EAN 4031582373394  
Order number 00061132



BETTER MOBILITY. BETTER LIFE.

## TECHNICAL DRAWINGS

---

