

# PURETECH AIR

DPR200x50-Ø20 2PR

EAN 4031582453010



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## WHEEL

Tread hardness	soft
Body material	Sheet Steel
Tread Material Mix	Pneumatic tyre, line profile
Bearing	Roller bearing
Threadguards	Without threadguard
Diameter	200 mm
Tread width	50 mm
Axle Hole Diameter	20 mm
Hub Length	58 mm
Hardness of tread (A)	55 Shore A

## PERFORMANCE

Roll Performance	● ○ ○ ○ ○
Movement Noise	● ● ● ○ ○
Attrition	● ● ● ● ○
Corrosion Resistance	● ● ● ○ ○

## CORE ATTRIBUTES

Product Name	Puretech air
Type	Wheel
Load capacity at 3 km/h	75 kg
Electric Conductive	No
Stainless	No
Load capacity Static	150 kg
Overall weight	0.68 kg

# PURETECH AIR

DPR200x50-Ø20 2PR

EAN 4031582453010



BETTER MOBILITY. BETTER LIFE.

## Product Drawings

