

LEVINA LIGHT

5220PJP075L51-10 RAL 9002

EAN 4031582482331



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ● ○
Attrition	● ● ● ○ ○
Corrosion resistance	● ● ● ● ○

CORE ATTRIBUTES

Product name	Levina light
Housing type	Swivel castor
Standard	EN12530 - Devices Castors
Load capacity at 3 km/h	75 kg
Load capacity Static	150 kg
Temperature range (Minimum)	-10 °C
Temperature range (Maximum)	40 °C
Overall height	103 mm
Overall weight	0.162 kg

WHEEL

Body material	Polypropylene
Tread material	Thermoplastic rubber
Bearing	Precision ball bearing
Threadguards	With threadguard
Diameter	75 mm
Tread width	25 mm
Hardness of tread (A)	87 Shore A

HOUSING

Material fork	Polyamide
Fork shape	Straight
Swivel bearing	Stem, swiveling
Offset	27 mm
Swivel radius	64.5 mm
Swivel interference	129 mm

FITTING

Fitting type	Blind hole for B10
Bolt hole diameter	10 mm

LEVINA LIGHT

5220PJP075L51-10 RAL 9002

EAN 4031582482331



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

