

# ELASTECH

IFP 200X50-Ø25

EAN 4031582319842

Broj porudžbine 00830632



BETTER MOBILITY. BETTER LIFE.



Slika se može razlikovati od originalnog proizvoda

## TOCAK

Materijal za telo	Aluminijum
	mekan
materijal omotaca	Elastična guma, neobeležena, vulkanizovana
Nošenje	precizini kuglični lezaj
Boja Tocak	Siva/ne-označavanje
stićnici omotaca	Bez stražara
Prečnik	200 mm
Širina omotac	50 mm
dimenzija rupa osovina	25 mm
dužina glavčine	60 mm
Širina tela	50 mm
Teškoća gazećeg omotac (A)	68 Šešelj A

## PERFORMANSE

Performanse kotrljanja ● ● ● ● ●

Buka u pokretu ● ● ● ● ●

Ishrana ● ● ● ● ●

otpornost na rdju ● ● ● ● ●

## OSNOVNI ATRIBUTI

Naziv proizvoda	Elastech
Tip	Tocak
Standard	EN12532 - transportna oprema
Nosivost na 4 km/h	450 kg
Nosivost na 6 km/h	360 kg
Statički Nosivost	900 kg
Temperaturni opseg (Minimalno)	-20 °C
Opseg temperature (maksimalni)	85 °C
Ukupna težina	1,709 kg

# ELASTECH

IFP 200X50-Ø25

EAN 4031582319842  
Broj porudžbine 00830632



BETTER MOBILITY. BETTER LIFE.

## TEHNIČKI CRTEŽI

