

# DURATECH

RK.TOP080X70-Ø47X14

EAN 4031582443103



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## WHEEL

Body material	Undefined
Tread material	Polypropylene, soft
Diameter	80 mm
Tread width	70 mm
Ball bearing diameter	47 mm
Ball bearing width	14 mm

## PERFORMANCE

Roll performance	● ● ● ● ●
Movement noise	● ● ● ○ ○
Attrition	● ● ● ● ●
Corrosion resistance	● ● ● ○ ○

## CORE ATTRIBUTES

Product name	Duratech
Type	Wheel
Load capacity at 3 km/h	650 kg
Load capacity Static	1300 kg
Temperature range (Minimum)	-40 °C
Temperature range (Maximum)	80 °C
Overall weight	0.25 kg

# DURATECH

RK.TOP080X70-Ø47X14

EAN 4031582443103



BETTER MOBILITY. BETTER LIFE.

## TECHNICAL DRAWINGS

