

# FOOTMASTER

FOOT MASTER GAPC-075-ASF-HUD

EAN 4031582496604  
Order number 00800206



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## PERFORMANCE

Roll performance	○ ○ ○ ○ ○
Movement noise	○ ○ ○ ○ ○
Attrition	○ ○ ○ ○ ○
Corrosion resistance	○ ○ ○ ○ ○

## CORE ATTRIBUTES

Product name	Footmaster
Type	Swivel castor
Load capacity at 3 km/h	100 kg
Temperature range (Minimum)	-10 °C
Temperature range (Maximum)	90 °C
Overall height	101 mm
Overall width	61 mm
Overall weight	1.546 kg

## WHEEL

Bearing	Unmachined hub
Diameter	75 mm
Tread width	30 mm
Body width	30 mm

## HOUSING

Offset	30 mm
Swivel radius	68 mm
Swivel interference	136 mm
Dome diameter	58 mm

## FITTING

Plate length	95 mm
Plate width	64 mm
Plate hole length (Minimum)	78 mm
Plate hole length (Maximum)	45 mm
Plate hole width (Minimum)	78 mm
Plate hole width (Maximum)	72 mm
Plate hole diameter	9 mm

# FOOTMASTER

FOOT MASTER GAPC-075-ASF-HUD

EAN 4031582496604  
Order number 00800206



BETTER MOBILITY. BETTER LIFE.

## TECHNICAL DRAWINGS

