

AGILA

2477DIK125P30-13 TFR

EAN 4031582394474



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ○ ○
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Agila
Housing type	Swivel castor with total lock
Standard	EN12530 - Devices Castors
Load capacity at 1.8 mph	220.46 lb
Load capacity Static	440.92 lb
Temperature range (Minimum)	-4 °F
Temperature range (Maximum)	185 °F
Overall height	6.3 in
Overall weight	2.68 lb

WHEEL

Body material	Sheet Steel
Tread material	Solid rubber, non-marking
Bearing	Cone ball bearing
Threadguards	With threadguard
Diameter	4.92 in
Tread width	1.26 in
Hardness of tread (A)	80 Shore A

HOUSING

Material	Steel sheet, medium
Fork shape	Broad
Swivel bearing	Two ball races
Offset	1.61 in
Swivel radius	5.16 in
Swivel interference	10.31 in

FITTING

Fitting type	Bolt hole
Bolt hole diameter	0.51 in
Hint	Castors can be mounted with standard screws of any length.

AGILA

2477DIK125P30-13 TFR

EAN 4031582394474



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

