

# MONO

5020PJH080S70-10X15 TFR

EAN 4031582385755



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ○ ○
Corrosion resistance	● ● ● ● ○

## CORE ATTRIBUTES

Product name	Mono
Type	Swivel castor
Standard	EN12528 - Furniture Castors
Load capacity at 3 km/h	70 kg
Load capacity Static	140 kg
Temperature range (Minimum)	-10 °C
Temperature range (Maximum)	40 °C
Overall height	110 mm
Overall weight	0.182 kg

## WHEEL

Body material	Polypropylene
Tread material	Thermoplastic rubber
Bearing	Plain bearing
Threadguards	With threadguard
Diameter	80 mm
Tread width	24 mm
Hardness of tread (A)	87 Shore A

## HOUSING

Material fork	Polyamide
Fork shape	Closed
Swivel bearing	Stem, swiveling
Offset	34 mm
Swivel radius	74 mm
Swivel interference	148 mm
Thread diameter	0 mm

## FITTING

Fitting type	Threaded stem with hexagon neck, top
Stem diameter	10 mm
Stem length	15 mm

PRODUCT INFORMATION

# MONO

5020PJH080S70-10X15 TFR

EAN 4031582385755



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

---

