

# ALPHA

3470PIO160P30-13

EAN 4031582303773



BETTER MOBILITY. BETTER LIFE.



Slika se može razlikovati od originalnog proizvoda

## PERFORMANSE

Performanse kotrljanja ●●●○○

Buka u pokretu ●●●○○

Ishrana ●●●○○

otpornost na rdju ●●●○○

## OSNOVNI ATRIBUTI

Naziv proizvoda	Alpha
Tip	Okretanje Tocak
Standard	EN12532 - transportna oprema
Nosivost na 4 km/h	135 kg
Statički Nosivost	270 kg
Temperaturni opseg (Minimalno)	-20 °C
Opseg temperature (maksimalni)	60 °C
Sveukupna visina	195 mm
Ukupna težina	1,884 kg

## TOCAK

Materijal za telo	polipropilen
materijal omotaca	Cvrsta guma, bez obeležavanja
Nošenje	klizni lezaj
osovina	Završena sa navrtkom
stitnici omotaca	Bez stražara
Prečnik	160 mm
Širina omotac	40 mm
Teškoća gazećeg omotac (A)	80 Šešelj A

## KUCISTE

Materijal	Čelični list, težak
oblik viljuska	siroko
okretni lezaj	Dve lopte
ofset	55 mm
okretni radijus	135 mm
Otpor okretanju	270 mm

## PRILAGOĐAVANJE

Tip uklapanja	otvor za vijak
dimenzija rupa sraf	13 mm

# ALPHA

3470PIO160P30-13

EAN 4031582303773



BETTER MOBILITY. BETTER LIFE.

## TEHNIČKI CRTEŽI

