

PURETECH

FVP 250x80-Ø30 HL90

EAN 4031582365429



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll Performance	● ● ● ● ●
Movement Noise	● ● ● ● ●
Attrition	● ● ● ● ●
Corrosion Resistance	● ● ● ● ●

CORE ATTRIBUTES

Product Name	Puretech
Type	Wheel
Standard	EN12533 - Heavy Duty Castors
Load capacity at 4 km/h	810 kg
Load capacity at 6 km/h	675 kg
Electric Conductive	No
Stainless	No
Load capacity Static	1350 kg
Temperature range (Minimum)	-20 °C
Temperature range (Maximum)	80 °C
Overall weight	6.9 kg

WHEEL

Tread hardness	soft
Body material	Cast iron
Tread Material Mix	Solid rubber, black
Bearing	Precision ball bearing
Wheel Color	Jet black (similar RAL9005)
Threadguards	With threadguard
Diameter	250 mm
Tread width	80 mm
Axle Hole Diameter	30 mm
Hub Length	90 mm
Body width	80 mm
Hardness of tread (A)	67 Shore A

PURETECH


FVP 250x80-Ø30 HL90

EAN 4031582365429

Order number 00836533
Product Drawings



BETTER MOBILITY. BETTER LIFE.




PRODUCT INFORMATION

PURETECH

FVP 250x80-Ø30 H190

EAN 4031582365429

Order number 10836533



BETTER MOBILITY. BETTER LIFE.