

# NOVATECH

ITP 150X50-Ø20 HL60

EAN 4031582319897

Broj porudžbine 00829121



BETTER MOBILITY. BETTER LIFE.



Slika se može razlikovati od originalnog proizvoda

## TOCAK

Materijal za telo	Aluminijum
materijal omotaca	Poliuretana, liveno
Nošenje	precizini kuglicni lezaj
Boja Tocak	Med žuta (RAL1005)
štitnici omotaca	Bez stražara
Prečnik	150 mm
Širina omotac	50 mm
dimenzija rupa osovina	20 mm
dužina glavcine	60 mm
Širina tela	50 mm
Teškoća gazećeg omotac (A)	92 Šor A
Teškoća gazećeg omotac (D)	42 Šor D

## PERFORMANSE

Performanse kotrljanja	● ● ● ● ○
Buka u pokretu	● ● ● ○ ○
Ishrana	● ● ● ● ○
otpornost na rdju	● ● ● ○ ○

## OSNOVNI ATRIBUTI

Naziv proizvoda	Novatech
Tip	Tocak
Standard	EN12532 - transportna oprema
Nosivost na 4 km/h	650 kg
Nosivost na 6 km/h	520 kg
Statički Nosivost	1300 kg
Temperaturni opseg (Minimalno)	-10 °C
Opseg temperature (maksimalni)	60 °C
Ukupna težina	1,177 kg

# NOVATECH

ITP 150X50-Ø20 HL60

EAN 4031582319897

Broj porudžbine 00829121



BETTER MOBILITY. BETTER LIFE.

## TEHNIČKI CRTEŽI

