

NOVATECH

ITP125X50-Ø20 HL60 SUPER CONVEX R25

EAN 4031582444650



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

WHEEL

Body material	Aluminium
Tread profile	convex
Tread material	Polyurethane, casted
Bearing	Precision ball bearing
Threadguards	Without threadguard
Diameter	125 mm
Tread width	50 mm
Axle hole diameter	20 mm
Hub length	60 mm
Hardness of tread (A)	92 Shore A

PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ● ○
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Novatech
Type	Wheel
Standard	EN12532 - Transport Equipment
Load capacity at 4 km/h	400 kg
Load capacity Static	800 kg
Temperature range (Minimum)	-20 °C
Temperature range (Maximum)	60 °C
Overall weight	0.818 kg

NOVATECH

ITP125X50-Ø20 HL60 SUPER CONVEX R25

EAN 4031582444650



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

