

# AGILA CARE US

2441XSX150R05-25.4 KICKSTOP

EAN 4031582388060



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## PERFORMANCE

|                      |           |
|----------------------|-----------|
| Roll performance     | ● ● ● ○ ○ |
| Movement noise       | ● ● ● ○ ○ |
| Attrition            | ● ● ● ○ ○ |
| Corrosion resistance | ● ● ● ○ ○ |

## CORE ATTRIBUTES

|                             |                                     |
|-----------------------------|-------------------------------------|
| Product name                | Agila care US                       |
| Housing type                | Swivel castor with directional lock |
| Standard                    | EN12530 - Devices Castors           |
| Load capacity at 3 km/h     | 150 kg                              |
| Electric conductive         | ✓                                   |
| Load capacity Static        | 300 kg                              |
| Temperature range (Minimum) | -40 °C                              |
| Temperature range (Maximum) | 80 °C                               |
| Overall height              | 193 mm                              |

## WHEEL

|                       |                                             |
|-----------------------|---------------------------------------------|
| Body material         | Polyamide, electric conductive              |
| Tread material        | Polyurethane, injected, electric-conductive |
| Bearing               | Precision ball bearing, sealed              |
| Threadguards          | With threadguard                            |
| Diameter              | 150 mm                                      |
| Tread width           | 32 mm                                       |
| Hardness of tread (D) | 40 Shore D                                  |

## HOUSING

|                     |                        |
|---------------------|------------------------|
| Material fork       | Steel sheet, medium    |
| Fork shape          | Broad                  |
| Swivel bearing      | Precision ball bearing |
| Offset              | 50 mm                  |
| Swivel interference | 324 mm                 |

## FITTING

|               |                   |
|---------------|-------------------|
| Fitting type  | Solid stem, round |
| Bolt diameter | 25.4 mm           |
| Bolt length   | 45 mm             |