

PURETECH

DIK 125X32-Ø8,1

EAN 4031582070163
Broj porudžbine 00000162

BETTER MOBILITY. BETTER LIFE.



Slika se može razlikovati od originalnog proizvoda

TOCAK

Materijal za telo	Čelik lista
materijal omotaca	Cvrsta guma, bez obeležavanja
Nošenje	konusi lezaj
Boja Tocak	plavo cinkovano
stirnici omotaca	Sa threadguard
Prečnik	125 mm
Širina omotac	32 mm
dimenzija rupa osovina	8 mm
duzina glavčine	36 mm
Širina tela	32 mm
Teškoća gazećeg omotac (A)	80 Šešelj A

PERFORMANSE

Performanse kotrljanja	● ● ● ○ ○
Buka u pokretu	● ● ● ○ ○
Ishrana	● ● ● ○ ○
otpornost na rdju	● ● ● ○ ○

OSNOVNI ATRIBUTI

Naziv proizvoda	Puretech
Tip	Tocak
Standard	EN12530 - Kastori uređaja
Nosivost na 3 km/h	100 kg
Statički Nosivost	200 kg
Temperaturni opseg (Minimalno)	-20 °C
Opseg temperature (maksimalni)	85 °C
Ukupna težina	0,614 kg

PURETECH

DIK 125X32-Ø8,1

EAN 4031582070163
Broj porudžbine 00000162



BETTER MOBILITY. BETTER LIFE.

TEHNIČKI CRTEŽI

