

# NOVATECH

RK.ETP085X80-Ø47X15,5

EAN 4031582369571



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## WHEEL

Body material	Undefined
Tread material	Polypropylene, soft
Diameter	85 mm
Tread width	80 mm
Hardness of tread (A)	92 Shore A
Ball bearing diameter	47 mm
Ball bearing width	15.5 mm

## PERFORMANCE

Roll performance	● ● ● ● ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ● ○
Corrosion resistance	● ● ● ○ ○

## CORE ATTRIBUTES

Product name	Novatech
Housing type	Wheel
Load capacity at 3 km/h	800 kg
Load capacity Static	1600 kg
Temperature range (Minimum)	-20 °C
Temperature range (Maximum)	60 °C

## TECHNICAL DRAWINGS

