

ELASTECH

SEP400X80-Ø40 HL80 TFR

EAN 4031582394412



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

WHEEL

Body material	Sheet steel, heavy
Tread hardness	soft
Tread material	Elastic tire, black, vulcanized
Bearing	Precision ball bearing
Threadguards	With threadguard
Diameter	400 mm
Tread width	80 mm
Axle hole diameter	40 mm
Hub length	80 mm
Hardness of tread (A)	70 Shore A

PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ○ ○
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Elastech
Type	Wheel
Standard	EN12533 - Heavy Duty Castors
Load capacity at 4 km/h	1440 kg
Load capacity at 6 km/h	1200 kg
Load capacity Static	2880 kg
Temperature range (Minimum)	-20 °C
Temperature range (Maximum)	85 °C
Overall weight	13.568 kg

ELASTECH

SEP400X80-Ø40 HL80 TFR

EAN 4031582394412



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

