

MAXTECH

UAP160X40-Ø20 HL60 RED

EAN 4031582322989



BETTER MOBILITY. BETTER LIFE.



Slika se može razlikovati od originalnog proizvoda

PERFORMANSE

Performanse kotrljanja	● ● ● ○ ○
Buka u pokretu	● ● ● ○ ○
Ishrana	● ● ● ● ○
otpornost na rdju	● ● ● ○ ○

OSNOVNI ATRIBUTI

Naziv proizvoda	Maxtech
Tip	Tocak
Standard	EN12532 - transportna oprema
Nosivost na 4 km/h	350 kg
Nosivost na 6 km/h	300 kg
Statički Nosivost	700 kg
Temperaturni opseg (Minimalno)	-40 °C
Opseg temperature (maksimalni)	80 °C
Ukupna težina	0,775 kg

TOCAK

Materijal za telo	poliamid
materijal omotaca	Poliuretan, liveno
Nošenje	precizini kuglicni lezaj
stitnici omotaca	Sa threadguard
Prečnik	160 mm
Širina omotac	40 mm
dimenzija rupa osovina	20 mm
dužina glavčine	60 mm
Teškoća gazećeg omotac (D)	60 Šor D

MAXTECH

UAP160X40-Ø20 HL60 RED

EAN 4031582322989



BETTER MOBILITY. BETTER LIFE.

TEHNIČKI CRTEŽI

