

FOOTMASTER

FOOT MASTER GAAD-100-ASF-HUD

EAN 4031582495164



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll Performance	○ ○ ○ ○ ○
Movement Noise	○ ○ ○ ○ ○
Attrition	○ ○ ○ ○ ○
Corrosion Resistance	○ ○ ○ ○ ○

CORE ATTRIBUTES

Product Name	Footmaster
Type	Swivel castor
Load capacity at 3 km/h	310 kg
Electric Conductive	No
Stainless	No
Temperature range (Minimum)	-10 °C
Temperature range (Maximum)	90 °C
Overall Height	160 mm
Overall width	118 mm
Overall weight	6.94 kg

HOUSING

Offset	30 mm
Swivel radius	84 mm
Swivel interference	168 mm
Dome diameter	104 mm

WHEEL

Bearing	Unmachined hub
Diameter	100 mm
Tread width	30 mm
Body width	30 mm

FITTING

Plate length	112 mm
Plate width	112 mm
Plate hole length (Maximum)	92 mm
Plate hole width (Maximum)	92 mm
Plate hole diameter	9 mm

FOOTMASTER

FOOT MASTER GAAD-100-ASF-HUD

EAN 4031582495164

Order number 00800109

Product Drawings



BETTER MOBILITY. BETTER LIFE.

