

# DURATECH

TOP 085X95-Ø20 HL95

EAN 4031582331271  
Broj porudžbine 00832617

BETTER MOBILITY. BETTER LIFE.



Slika se može razlikovati od originalnog proizvoda

## TOCAK

Materijal za telo	poliamid težak
materijal omotaca	Identično sa telom Tocak
Nošenje	precizini kuglicni lezaj
Boja Tocak	Prirodno belo
stitnici omotaca	Bez stražara
Prečnik	85 mm
Širina omotac	95 mm
dimenzija rupa osovina	20 mm
dužina glavcine	95 mm
Širina tela	95 mm
Teškoća gazećeg omotac (D)	75 Šor D
Tip ležaja	6204

## PERFORMANSE

Performanse kotrljanja	● ● ● ● ●
Buka u pokretu	● ● ○ ○ ○
Ishrana	● ● ● ● ●
otpornost na rdju	● ● ● ○ ○

## OSNOVNI ATRIBUTI

Naziv proizvoda	Duratech
Tip	Tocak
Standard	EN12533 - Tockoviza teske terete
Nosivost na 4 km/h	900 kg
Nosivost na 6 km/h	720 kg
Statički Nosivost	1800 kg
Temperaturni opseg (Minimalno)	-40 °C
Opseg temperature (maksimalni)	80 °C
Ukupna težina	0,577 kg

# DURATECH

TOP 085X95-Ø20 HL95

EAN 4031582331271  
Broj porudžbine 00832617



BETTER MOBILITY. BETTER LIFE.

## TEHNIČKI CRTEŽI

