

# MONO

A025PJH080S70-10X25

EAN 4031582456349



BETTER MOBILITY. BETTER LIFE.

## PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ○ ○
Corrosion resistance	● ● ● ○ ○

## CORE ATTRIBUTES

Product name	Mono
Housing type	Swivel castor with wheel brake
Standard	EN12528 - Furniture Castors
Load capacity at 3 km/h	40 kg
Load capacity Static	80 kg
Temperature range (Minimum)	-10 °C
Temperature range (Maximum)	40 °C
Overall height	112 mm
Overall weight	0.139 kg

## WHEEL

Body material	Polypropylene
Tread material	Thermoplastic rubber
Bearing	Plain bearing
Threadguards	With threadguard
Diameter	80 mm
Tread width	24 mm
Hardness of tread (A)	87 Shore A

## HOUSING

Material fork	Polypropylene
Fork shape	Closed
Swivel bearing	Stem, swiveling
Offset	34 mm
Swivel radius	74 mm
Swivel interference	148 mm
Thread diameter	10 mm

## FITTING

Fitting type	Threaded stem with hexagon neck, top
Stem length	25 mm

# MONO

A025PJH080S70-10X25

EAN 4031582456349



BETTER MOBILITY. BETTER LIFE.

## TECHNICAL DRAWINGS

---

