

DURATECH

TOP 085X75-Ø20 HL75

EAN 4031582331196
Order number 00832613



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

WHEEL

Body material	Polyamide, heavy
Tread material	Identical with wheel body
Bearing	Precision ball bearing
Wheel color	Natural white
Threadguards	Without threadguard
Diameter	85 mm
Tread width	75 mm
Axle hole diameter	20 mm
Hub length	75 mm
Body width	75 mm
Hardness of tread (D)	75 Shore D
Bearing type	6204

PERFORMANCE

Roll performance	● ● ● ● ●
Movement noise	● ● ○ ○ ○
Attrition	● ● ● ● ●
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Duratech
Type	Wheel
Standard	EN12533 - Heavy Duty Castors
Load capacity at 4 km/h	750 kg
Load capacity at 6 km/h	600 kg
Load capacity Static	1500 kg
Temperature range (Minimum)	-40 °C
Temperature range (Maximum)	80 °C
Overall weight	0.208 kg

DURATECH

TOP 085X75-Ø20 HL75

EAN 4031582331196
Order number 00832613



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

