

# MAXTECH

PNP200X45-Ø8 MS

EAN 4031582320640



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## WHEEL

Body material	Polypropylene
Tread material	Polyurethane, foamed
Bearing	Precision ball bearing
Threadguards	With threadguard
Diameter	7.87 in
Tread width	1.77 in
Axle hole diameter	0.31 in
Hub length	2.09 in
Hardness of tread (A)	70 Shore A

## PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ○ ○
Corrosion resistance	● ● ● ○ ○

## CORE ATTRIBUTES

Product name	Maxtech
Housing type	Wheel
Standard	EN12530 - Devices Castors
Load capacity at 1.8 mph	154.32 lb
Load capacity Static	308.65 lb
Temperature range (Minimum)	-4 °F
Temperature range (Maximum)	140 °F
Overall weight	1.22 lb

# MAXTECH

PNP200X45-Ø8 MS

EAN 4031582320640



BETTER MOBILITY. BETTER LIFE.

## TECHNICAL DRAWINGS

---

