

PRODUCT INFORMATION

SUPRATECH

PJP125x40-Ø 8,3, blue

EAN 4031582444216



Image may differ from the original product

PERFORMANCE

Roll Performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ○ ○
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Supratech
Type	Wheel
Standard	EN12532 - Transport Equipment
Load capacity at 2.5 mph	396.83 lb
Electric conductive	no
Stainless	no
Load capacity Static	793.66 lb
Temperature range (Minimum)	-4 °F
Temperature range (Maximum)	140 °F
Overall weight	0.53 lb



BETTER MOBILITY. BETTER LIFE.

WHEEL

Tread hardness	soft
Body material	Polypropylene
Tread material	Thermoplastic rubber
Bearing	Precision ball bearing
Threadguards	With threadguard
Diameter	4.92 in
Tread width	1.57 in
Axle hole diameter	0.31 in
Hub length	1.77 in
Hardness of tread (A)	65 Shore A

SUPRATECH

PJP125x40-Ø 8,3, blue

EAN 4031582444216



BETTER MOBILITY. BETTER LIFE.

Product Drawings

