PRODUCT INFORMATION

NOVATECH

RK.ETP075x50-Ø47x12

EAN 4031582369496

BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

WHEEL

Body material	Undefined
Tread material	Polypropylene, soft
Diameter	2.95 in
Tread width	1.97 in
Hardness of tread (A)	92 Shore A
Ball bearing diameter	1.85 in
Ball bearing width	0.47 in

PERFORMANCE

Roll Performance	●●●●○
Movement noise	●●●○○
Attrition	●●●●○
Corrosion resistance	●●●○○

CORE ATTRIBUTES

Product name	Novatech
Type	Wheel
Load capacity at 1.8 mph	1102.31 lb
Electric conductive	no
Stainless	no
Load capacity Static	2204.62 lb
Temperature range (Minimum)	-4 °F
Temperature range (Maximum)	140 °F
Overall weight	1.21 lb

© Copyright 2026 TENTE International GmbH

NOVATECH

RK.ETP075x50-Ø47x12

EAN 4031582369496

BETTER MOBILITY. BETTER LIFE.

Product Drawings





