PRODUCT INFORMATION

ELASTECH

EEZ 200x75-Ø100 DG

EAN 4031582318333



Image may differ from the original product

PERFORMANCE

Roll Performance	●●○○○
Movement noise	●●●●●
Attrition	●●●○○
Corrosion resistance	●●●○○

CORE ATTRIBUTES

Product name	Elastech
Type	Wheel
Standard	EN12533 - Heavy Duty Castors
Load capacity at 2.5 mph	1322.77 lb
Load capacity at 3.7 mph	1102.31 lb
Electric conductive	no
Stainless	no
Load capacity Static	2204.62 lb
Temperature range (Minimum)	-4 °F
Temperature range (Maximum)	185 °F
Overall weight	5.08 lb

WHEEL

Tread hardness	soft
Body material	Steel, iron
Tread material	Elastic tire, black, vulcanized
Bearing	Borehole, unmachined
Wheel color	Jet black (similar RAL9005)
Diameter	7.87 in
Tread width	2.95 in
Axle hole diameter	3.94 in
Hub length	2.95 in
Body width	2.95 in
Hardness of tread (A)	68 Shore A

© Copyright 2026 TENTE International GmbH


ELASTECH

EEZ 200x75-Ø100 DG

EAN 4031582318333

Order number 00830872

Product Drawings




© Copyright 2026 TENTE International GmbH

ELASTECH

EEZ 200x75-Ø100 DG

EAN 4031582318333

Order number 00830872



BETTER MOBILITY. BETTER LIFE.

© Copyright 2026 TENTE International GmbH