PRODUCT INFORMATION

# AGILA

## 2477DYK100R07-Ø19-21,5

EAN 4031582342031



Image may differ from the original product

### PERFORMANCE

| | |
|---|---|
| Roll Performance | ●●●○○ |
| Movement noise | ●●●○○ |
| Attrition | ●●●○○ |
| Corrosion resistance | ●●●○○ |

### CORE ATTRIBUTES

| | |
|---|---|
| Product name | Agila |
| Type | Swivel caster with total lock |
| Standard | EN12530 - Devices Castors |
| Load capacity at 1.8 mph | 176.37 lb |
| Electric conductive | Yes |
| Stainless | no |
| Load capacity Static | 352.74 lb |
| Temperature range (Minimum) | 14 °F |
| Temperature range (Maximum) | 104 °F |
| Overall height | 5.43 in |
| Overall weight | 2.45 lb |

### HOUSING

| | |
|---|---|
| Housing Material | Steel sheet, medium |
| Fork shape | Broad |
| Swivel bearing | Two ball races |
| Housing Color | Blue passivated |
| Offset | 1.71 in |
| Swivel radius | 5.16 in |
| Swivel interference | 10.31 in |

### WHEEL

| | |
|---|---|
| Body material | Sheet Steel |
| Tread material | Solid rubber, black, electric-conductive |
| Bearing | Cone ball bearing |
| Threadguards | With threadguard |
| Diameter | 3.94 in |
| Tread width | 1.26 in |
| Hardness of tread (A) | 80 Shore A |

### FITTING

| | |
|---|---|
| Fitting type | Synthetic expander, round |
| Expander fitting (Minimum) | 0.75 in |
| Expander fitting (Maximum) | 0.85 in |
| Hint | Please indicate required tube innerdiameter when ordering. |

© Copyright 2026 TENTE International GmbH


# AGILA

2477DYK100R07-Ø19-21,5

EAN 4031582342031

BETTER MOBILITY. BETTER LIFE.

## Product Drawings




© Copyright 2026 TENTE International GmbH