

# ELASTECH

IEP 250X50-Ø20 HL60

EAN 4031582319750

Broj porudžbine 00801772



BETTER MOBILITY. BETTER LIFE.



Slika se može razlikovati od originalnog proizvoda

## TOCAK

Materijal za telo	Aluminijum
	mekan
materijal omotaca	Elastična guma, crna, vulkanizovana
Nošenje	precizini kuglični lezaj
Boja Tocak	Crni mlaz (sličan RAL9005)
štitnici omotaca	Bez stražara
Prečnik	250 mm
Širina omotac	50 mm
dimenzija rupa osovina	20 mm
dužina glavčine	60 mm
Širina tela	50 mm
Teškoća gazećeg omotac (A)	68 Šešelj A

## PERFORMANSE

Performanse kotrljanja	● ● ● ● ●
Buka u pokretu	● ● ● ● ●
Ishrana	● ● ● ● ●
otpornost na rdju	● ● ● ● ●

## OSNOVNI ATRIBUTI

Naziv proizvoda	Elastech
Tip	Tocak
Standard	EN12532 - transportna oprema
Nosivost na 4 km/h	500 kg
Nosivost na 6 km/h	400 kg
Statički Nosivost	1000 kg
Temperaturni opseg (Minimalno)	-20 °C
Opseg temperature (maksimalni)	85 °C
Ukupna težina	2,37 kg

# ELASTECH

IEP 250X50-Ø20 HL60

EAN 4031582319750  
Broj porudžbine 00801772



BETTER MOBILITY. BETTER LIFE.

## TEHNIČKI CRTEŽI

