

# LEVINA CARE

5344PJP125R36-32S35 D 9002 4XM6

Order number 00066684



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## PERFORMANCE

|                      |           |
|----------------------|-----------|
| Roll performance     | ● ● ● ○ ○ |
| Movement noise       | ● ● ● ● ○ |
| Attrition            | ● ● ● ○ ○ |
| Corrosion resistance | ● ● ● ● ○ |

## CORE ATTRIBUTES

|                             |                                                       |
|-----------------------------|-------------------------------------------------------|
| Product name                | Levina care                                           |
| Housing type                | Swivel castor with central, total or directional lock |
| Standard                    | EN12530 - Devices Castors                             |
| Load capacity at 3 km/h     | 100 kg                                                |
| Load capacity Static        | 200 kg                                                |
| Temperature range (Minimum) | -10 °C                                                |
| Temperature range (Maximum) | 40 °C                                                 |
| Overall height              | 161 mm                                                |
| Overall width               | 59 mm                                                 |
| Overall weight              | 0.708 kg                                              |

## WHEEL

|                       |                        |
|-----------------------|------------------------|
| Body material         | Polypropylene          |
| Tread material        | Thermoplastic rubber   |
| Bearing               | Precision ball bearing |
| Tread color           | Iron grey (RAL7011)    |
| Wheel color           | Grey white (RAL9002)   |
| Threadguards          | With threadguard       |
| Diameter              | 125 mm                 |
| Tread width           | 32 mm                  |
| Body width            | 32 mm                  |
| Hardness of tread (A) | 83 Shore A             |

## HOUSING

|                     |                        |
|---------------------|------------------------|
| Material fork       | Polyamide              |
| Fork shape          | Slim                   |
| Swivel bearing      | Precision ball bearing |
| Colour              | Grey white (RAL9002)   |
| Offset              | 38 mm                  |
| Swivel radius       | 100.5 mm               |
| Swivel interference | 201 mm                 |
| Dome diameter       | 59 mm                  |

## FITTING

|                              |                                                    |
|------------------------------|----------------------------------------------------|
| Fitting type                 | Stem with cam hole for profile bars, short version |
| Bolt diameter                | 32 mm                                              |
| Bolt length                  | 51 mm                                              |
| Bolt thread position         | 7 mm                                               |
| Bolt mounting holes quantity | 4                                                  |