

LINEA CLINIC

5944UAC150R36-32S30 CC R9002

EAN 4031582382860



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

| | |
|----------------------|-----------|
| Roll performance | ● ● ● ● ● |
| Movement noise | ● ● ● ○ ○ |
| Attrition | ● ● ● ● ○ |
| Corrosion resistance | ● ● ● ● ○ |

CORE ATTRIBUTES

| | |
|-----------------------------|---|
| Product name | Linea clinic |
| Type | Swivel castor with central, total or directional lock |
| Standard | similar EN12531- Hospital Bed Castors |
| Load capacity at 3 km/h | 150 kg |
| Load capacity at 4 km/h | 150 kg |
| Stainless | ✓ |
| Load capacity Static | 300 kg |
| Temperature range (Minimum) | -10 °C |
| Temperature range (Maximum) | 40 °C |
| Overall height | 155 mm |
| Overall width | 71 mm |
| Overall weight | 1.16 kg |

Certification Tested and monitored by TÜV Süd



Deutscher Designer Club



interzum Award



IF Design Award

WHEEL

| | |
|-----------------------|-----------------------------------|
| Body material | Polyamide |
| Tread material | Polyurethane, injected |
| Bearing | Precision ball bearing, stainless |
| Threadguards | With threadguard |
| Diameter | 150 mm |
| Tread width | 15 mm |
| Hardness of tread (A) | 92 Shore A |

HOUSING

| | |
|---------------------|---|
| Material fork | Polyamide |
| Fork shape | Twin wheel housing |
| Swivel bearing | Precision ball bearing |
| Offset | 47.5 mm |
| Swivel radius | 122.5 mm |
| Swivel interference | 254 mm |
| Hint | Housing with integrated cable catcher made of Polyethylene. |

FITTING

| | |
|---------------|--|
| Brake cam | hex cam |
| Fitting type | Stem with cam hole for profile bars, short version |
| Bolt diameter | 32 mm |
| Bolt length | 50 mm |
| Hint | Washable beds must be sealed in the fitting area by the hospital bed manufacturer. |

PRODUCT INFORMATION

LINEA CLINIC

5944UAC150R36-32S30 CC R9002

EAN 4031582382860



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

