

# SUPRATECH

PJI050X19-Ø8 AMARILLA

EAN 4031582457278



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## WHEEL

Body material	Polypropylene
Tread material	Thermoplastic rubber
Bearing	Plain bearing with spacer tube
Threadguards	Without threadguard
Diameter	50 mm
Tread width	19 mm
Axle hole diameter	6 mm
Hub length	21.5 mm
Hardness of tread (A)	87 Shore A

## PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ○ ○
Corrosion resistance	● ● ● ○ ○

## CORE ATTRIBUTES

Product name	Supratech
Housing type	Wheel
Standard	EN12530 - Devices Castors
Load capacity at 3 km/h	40 kg
Load capacity Static	80 kg
Temperature range (Minimum)	-20 °C
Temperature range (Maximum)	60 °C
Overall weight	0.021 kg

# SUPRATECH

PJI050X19-Ø8 AMARILLA

EAN 4031582457278



BETTER MOBILITY. BETTER LIFE.

## TECHNICAL DRAWINGS

---

