

MAXTECH

UAP100X40-Ø15 HL44 BURDEOS

EAN 4031582442564



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

WHEEL

| | |
|-----------------------|------------------------|
| Body material | Polyamide |
| Tread material | Polyurethane, injected |
| Bearing | Precision ball bearing |
| Threadguards | With threadguard |
| Diameter | 3.94 in |
| Tread width | 1.57 in |
| Axle hole diameter | 0.59 in |
| Hub length | 1.73 in |
| Hardness of tread (D) | 40 Shore D |

PERFORMANCE

| | |
|----------------------|-----------|
| Roll performance | ● ● ● ○ ○ |
| Movement noise | ● ● ● ○ ○ |
| Attrition | ● ● ● ● ○ |
| Corrosion resistance | ● ● ● ○ ○ |

CORE ATTRIBUTES

| | |
|-----------------------------|---------------------------|
| Product name | Maxtech |
| Type | Wheel |
| Standard | EN12530 - Devices Castors |
| Load capacity at 1.8 mph | 330.69 lb |
| Load capacity Static | 661.39 lb |
| Temperature range (Minimum) | -40 °F |
| Temperature range (Maximum) | 176 °F |
| Overall weight | 0.51 lb |

MAXTECH

UAP100X40-Ø15 HL44 BURDEOS

EAN 4031582442564



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

