

# MAXTECH

PNP 200X50-Ø8 HL60

EAN 4031582320657

Broj porudžbine 00005570



BETTER MOBILITY. BETTER LIFE.



Slika se može razlikovati od originalnog proizvoda

## TOCAK

|                            |                          |
|----------------------------|--------------------------|
| Materijal za telo          | polipropilen             |
|                            | mekan                    |
| materijal omotaca          | Poliuretanski, penasti   |
| Nošenje                    | precizini kuglicni lezaj |
| Boja Tocak                 | Crna                     |
| štيتnici omotaca           | Sa threadguard           |
| Prečnik                    | 200 mm                   |
| Širina omotac              | 50 mm                    |
| dimenzija rupa osovina     | 8 mm                     |
| duzina glavčine            | 60 mm                    |
| Širina tela                | 50 mm                    |
| Teškoća gazećeg omotac (A) | 70 Šešelj A              |

## PERFORMANSE

|                        |           |
|------------------------|-----------|
| Performanse kotrljanja | ● ● ● ○ ○ |
| Buka u pokretu         | ● ● ● ● ○ |
| Ishrana                | ● ● ● ○ ○ |
| otpornost na rdju      | ● ● ● ○ ○ |

## OSNOVNI ATRIBUTI

|                                |                              |
|--------------------------------|------------------------------|
| Naziv proizvoda                | Maxtech                      |
| Tip                            | Tocak                        |
| Standard                       | EN12532 - transportna oprema |
| Nosivost na 4 km/h             | 75 kg                        |
| Statički Nosivost              | 150 kg                       |
| Temperaturni opseg (Minimalno) | -20 °C                       |
| Opseg temperature (maksimalni) | 60 °C                        |
| Ukupna težina                  | 0,66 kg                      |

# MAXTECH

PNP 200X50-Ø8 HL60

EAN 4031582320657

Broj porudžbine 00005570



BETTER MOBILITY. BETTER LIFE.

## TEHNIČKI CRTEŽI

---

