

# ELASTECH

UFR160X46-Ø25 TFR

EAN 4031582390681



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## WHEEL

Body material	Polyamide
	soft
Tread material	Elastic tire, non-marking, vulcanized
Bearing	Roller bearing
Threadguards	Without threadguard
Diameter	6.3 in
Tread width	1.81 in
Axle hole diameter	0.98 in
Hub length	2.28 in
Hardness of tread (A)	65 Shore A

## PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ● ●
Attrition	● ● ● ○ ○
Corrosion resistance	● ● ● ○ ○

## CORE ATTRIBUTES

Product name	Elastech
Type	Wheel
Standard	EN12532 - Transport Equipment
Load capacity at 2.5 mph	661.39 lb
Load capacity Static	1322.77 lb
Temperature range (Minimum)	-4 °F
Temperature range (Maximum)	176 °F
Overall weight	1.63 lb

# ELASTECH

UFR160X46-Ø25 TFR

EAN 4031582390681



BETTER MOBILITY. BETTER LIFE.

## TECHNICAL DRAWINGS

---

