

# MONO

5020PJH080S70-10X15 TFR

EAN 4031582385755



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## PERFORMANCE

|                      |           |
|----------------------|-----------|
| Roll performance     | ● ● ● ○ ○ |
| Movement noise       | ● ● ● ○ ○ |
| Attrition            | ● ● ● ○ ○ |
| Corrosion resistance | ● ● ● ● ○ |

## CORE ATTRIBUTES

|                             |                             |
|-----------------------------|-----------------------------|
| Product name                | Mono                        |
| Housing type                | Swivel castor               |
| Standard                    | EN12528 - Furniture Castors |
| Load capacity at 1.8 mph    | 154.32 lb                   |
| Load capacity Static        | 308.65 lb                   |
| Temperature range (Minimum) | 14 °F                       |
| Temperature range (Maximum) | 104 °F                      |
| Overall height              | 4.33 in                     |
| Overall weight              | 0.4 lb                      |

## WHEEL

|                       |                      |
|-----------------------|----------------------|
| Body material         | Polypropylene        |
| Tread material        | Thermoplastic rubber |
| Bearing               | Plain bearing        |
| Threadguards          | With threadguard     |
| Diameter              | 3.15 in              |
| Tread width           | 0.94 in              |
| Hardness of tread (A) | 87 Shore A           |

## HOUSING

|                     |                 |
|---------------------|-----------------|
| Material            | Polyamide       |
| Fork shape          | Closed          |
| Swivel bearing      | Stem, swiveling |
| Offset              | 1.34 in         |
| Swivel radius       | 2.91 in         |
| Swivel interference | 5.83 in         |
| Thread diameter     | 0 in            |

## FITTING

|              |                                      |
|--------------|--------------------------------------|
| Fitting type | Threaded stem with hexagon neck, top |
| Stem length  | 0.59 in                              |

PRODUCT INFORMATION

# MONO

5020PJH080S70-10X15 TFR

EAN 4031582385755



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

---

