

# MONO

5020PJH080S70-10X15 TFR

EAN 4031582385755



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ○ ○
Corrosion resistance	● ● ● ● ○

## CORE ATTRIBUTES

Product name	Mono
Type	Swivel castor
Standard	EN12528 - Furniture Castors
Load capacity at 1.8 mph	154.32 lb
Load capacity Static	308.65 lb
Temperature range (Minimum)	14 °F
Temperature range (Maximum)	104 °F
Overall height	4.33 in
Overall weight	0.4 lb

## WHEEL

Body material	Polypropylene
Tread material	Thermoplastic rubber
Bearing	Plain bearing
Threadguards	With threadguard
Diameter	3.15 in
Tread width	0.94 in
Hardness of tread (A)	87 Shore A

## HOUSING

Material	Polyamide
Fork shape	Closed
Swivel bearing	Stem, swiveling
Offset	1.34 in
Swivel radius	2.91 in
Swivel interference	5.83 in
Thread diameter	0 in

## FITTING

Fitting type	Threaded stem with hexagon neck, top
Stem diameter	0.39 in
Stem length	0.59 in

PRODUCT INFORMATION

# MONO

5020PJH080S70-10X15 TFR

EAN 4031582385755



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

---

