

PRODUCT INFORMATION

PURETECH AIR

DPP400x100-Ø25 HL74 2PR

EAN 4031582317831



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

WHEEL

Tread hardness	soft
Body material	Sheet Steel
Tread material	Pneumatic tire, line profile
Bearing	Precision ball bearing
Threadguards	With threadguard
Diameter	15.75 in
Tread width	3.94 in
Axle hole diameter	0.98 in
Hub length	2.91 in
Hardness of tread (A)	55 Shore A

PERFORMANCE

Roll Performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ○ ○
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Puretech air
Type	Wheel
Load capacity at 1.8 mph	440.92 lb
Electric conductive	no
Stainless	no
Load capacity Static	881.85 lb
Overall weight	5.4 lb

PURETECH AIR

DPP400x100-Ø25 HL74 2PR

EAN 4031582317831



BETTER MOBILITY. BETTER LIFE.

Product Drawings

