

## GALEA

5077PJP125P60-90X70

EAN 4031582367911



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## PERFORMANCE

|                      |           |
|----------------------|-----------|
| Roll performance     | ● ● ● ○ ○ |
| Movement noise       | ● ● ● ○ ○ |
| Attrition            | ● ● ● ○ ○ |
| Corrosion resistance | ● ● ● ● ○ |

## CORE ATTRIBUTES

|                             |                               |
|-----------------------------|-------------------------------|
| Product name                | Galea                         |
| Type                        | Swivel castor with total lock |
| Standard                    | EN12530 - Devices Castors     |
| Load capacity at 3 km/h     | 100 kg                        |
| Load capacity Static        | 200 kg                        |
| Temperature range (Minimum) | -20 °C                        |
| Temperature range (Maximum) | 60 °C                         |
| Overall height              | 163 mm                        |
| Overall weight              | 0.414 kg                      |

## WHEEL

|                       |                        |
|-----------------------|------------------------|
| Body material         | Polypropylene          |
| Tread material        | Thermoplastic rubber   |
| Bearing               | Precision ball bearing |
| Threadguards          | With threadguard       |
| Diameter              | 125 mm                 |
| Tread width           | 30 mm                  |
| Hardness of tread (A) | 87 Shore A             |

## HOUSING

|                     |                |
|---------------------|----------------|
| Material fork       | Polyamide      |
| Fork shape          | Closed         |
| Swivel bearing      | Two ball races |
| Offset              | 40 mm          |
| Swivel interference | 205 mm         |

## FITTING

|                             |                   |
|-----------------------------|-------------------|
| Fitting type                | Rectangular plate |
| Plate length                | 90 mm             |
| Plate width                 | 70 mm             |
| Plate hole length (Minimum) | 60 mm             |
| Plate hole length (Maximum) | 70 mm             |
| Plate hole width (Minimum)  | 50 mm             |
| Plate hole width (Maximum)  | 55 mm             |
| Plate hole diameter         | 8 mm              |

## PRODUCT INFORMATION

# GALEA

5077PJP125P60-90X70

EAN 4031582367911

## TECHNICAL DRAWINGS

---

