PRODUCT INFORMATION

NOVATECH

RK.ETP082x100-Ø47x12

EAN 4031582369557

BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

WHEEL

Body material	Undefined
Tread Material Mix	Polypropylene, soft
Diameter	82 mm
Tread width	100 mm
Hardness of tread (A)	92 Shore A
Ball bearing diameter	47 mm
Ball bearing width	12 mm

PERFORMANCE

Roll Performance	●●●●○
Movement Noise	●●●○○
Attrition	●●●●○
Corrosion Resistance	●●●○○

CORE ATTRIBUTES

Product Name	Novatech
Type	Wheel
Load capacity at 3 km/h	800 kg
Electric Conductive	No
Stainless	No
Load capacity Static	1600 kg
Temperature range (Minimum)	-20 °C
Temperature range (Maximum)	60 °C

© Copyright 2026 TENTE International GmbH


NOVATECH


RK.ETP082x100-Ø47x12


EAN 4031582369557

BETTER MOBILITY. BETTER LIFE.

Product Drawings







© Copyright 2026 TENTE International GmbH