

AGILA STAINLESS

7477PJO125P50

EAN 4031582349948



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll Performance	● ● ● ● ○ ○
Movement noise	● ● ● ● ○ ○
Attrition	● ● ● ● ○ ○
Corrosion resistance	● ● ● ● ● ●

CORE ATTRIBUTES

Product name	Agila stainless
Type	Swivel caster with total lock
Standard	EN12530 - Devices Castors
Load capacity at 1.8 mph	220.46 lb
Electric conductive	no
Stainless	Yes
Load capacity Static	440.92 lb
Temperature range (Minimum)	-4 °F
Temperature range (Maximum)	140 °F
Overall height	6.3 in
Overall width	2.36 in
Overall weight	1.77 lb

HOUSING

Housing Material	Stainless steel, medium
Fork shape	Broad
Swivel bearing	Two ball races
Housing Color	Stainless steel
Offset	1.61 in
Swivel radius	5.16 in
Swivel interference	10.31 in
Dome diameter	2.36 in

WHEEL

Body material	Polypropylene
Tread material	Thermoplastic rubber
Bearing	Plain bearing
Wheel color	Silver gray (RAL7001)
Threadguards	Without threadguard
Diameter	4.92 in
Tread width	1.26 in
Body width	1.26 in
Hardness of tread (A)	87 Shore A

FITTING

Fitting type	Rectangular plate
Plate length	3.03 in
Plate width	2.64 in
Plate hole length (Minimum)	1.83 in
Plate hole length (Maximum)	2.03 in
Plate hole width (Minimum)	2.2 in
Plate hole width (Maximum)	2.42 in
Plate hole diameter	0.33 in

AGILA STAINLESS

7477PJO125P50

EAN 4031582349948

Order number 00036333

Product Drawings



BETTER MOBILITY. BETTER LIFE.

