

DURATECH

TOP 065x32-Ø12 HL32

EAN 4031582332315



BETTER MOBILITY. BETTER LIFE.



Slika se može razlikovati od originalnog proizvoda

TOCAK


Materijal za telo	poliamid težak
materijal omotaca	Identično sa telom Tocak
Nošenje	precizini kuglicni lezaj
Boja Tocak	Prirodno belo
stitnici omotaca	Bez stražara
Prečnik	65 mm
Širina omotac	32 mm
dimenzija rupa osovina	12 mm
dužina glavnice	32 mm
Širina tela	32 mm
Teškoća gazećeg omotac (D)	75 Šor D
Tip ležaja	6201

PERFORMANSE

Performanse kotrljanja	● ● ● ● ●
Buka u pokretu	● ● ○ ○ ○
Ishrana	● ● ● ● ●
otpornost na rdju	● ● ● ○ ○

OSNOVNI ATRIBUTI

Naziv proizvoda	Duratech
Tip	Tocak
Standard	EN12532 - transportna oprema
Nosivost na 4 km/h	290 kg
Nosivost na 6 km/h	240 kg
Električni provod	no
nerdjajući	no
Statički Nosivost	480 kg
Temperaturni opseg (Minimalno)	-40 °C
Opseg temperature (maksimalni)	80 °C
Ukupna težina	0.17 kg




DURATECH

TOP 065x32-Ø12-HL32

EAN 4031582382315

Broj porudžbine 00525018



BETTER MOBILITY. BETTER LIFE.