

STEM

B40 - 11x20 / 10

EAN 4031582418002



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Corrosion resistance ● ● ● ○ ○

CORE ATTRIBUTES

Product name	Stem
Type	Accessory
Load capacity at 1.8 mph	132.28 lb
Electric conductive	no
Stainless	no
Load capacity Static	264.55 lb
Overall height	0.18 in
Overall weight	0.08 lb

FITTING

Fitting type	Stem with systhetic circlip, with collar
Stem diameter	0.43 in