PRODUCT INFORMATION

MAXTECH

UAR 080x38-Ø12 HL44,4 7001/7015

EAN 4031582323085



Image may differ from the original product

WHEEL

Body material	Polyamide
Tread Material Mix	Polyurethane, injected
Bearing	Roller bearing
Wheel Color	Silver grey (RAL7001)
Threadguards	Without threadguard
Diameter	80 mm
Tread width	38 mm
Axle Hole Diameter	12 mm
Hub Length	44.4 mm
Body width	38 mm
Hardness of tread (A)	92 Shore A
Hardness of tread (D)	42 Shore D

PERFORMANCE

Roll Performance	●●●○○
Movement Noise	●●●○○
Attrition	●●●●○
Corrosion Resistance	●●●○○

CORE ATTRIBUTES

Product Name	Maxtech
Type	Wheel
Standard	EN12532 - Transport Equipment
Load capacity at 4 km/h	150 kg
Electric Conductive	No
Stainless	No
Load capacity Static	300 kg
Temperature range (Minimum)	-25 °C
Temperature range (Maximum)	80 °C
Overall weight	0.19 kg

© Copyright 2026 TENTE International GmbH


MAXTECH

UAR 080x38-Ø12 HL44,4 7001/7015

EAN 4031582323085

Order number 00007010

Product Drawings



© Copyright 2026 TENTE International GmbH