

PURETECH

FVP300X85-25

EAN 4031582429732



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

WHEEL

Body material	Casting
	soft
Tread material	Solid rubber, black
Bearing	Precision ball bearing
Threadguards	With threadguard
Diameter	11.81 in
Tread width	3.35 in
Axle hole diameter	0.98 in
Hub length	3.62 in
Hardness of tread (A)	67 Shore A

PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ○ ○ ○
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Puretech
Type	Wheel
Standard	EN12533 - Heavy Duty Castors
Load capacity at 2.5 mph	2116.44 lb
Load capacity at 3.7 mph	1763.7 lb
Load capacity Static	4232.87 lb
Temperature range (Minimum)	-4 °F
Temperature range (Maximum)	176 °F
Overall weight	31.83 lb

PURETECH

FVP300X85-25

EAN 4031582429732



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

