PRODUCT INFORMATION

PURETECH

PVR 080x35-Ø12 HL44,4

EAN 4031582321241



Image may differ from the original product

WHEEL

Body material	Polypropylene
Tread material	Solid rubber, black
Bearing	Roller bearing
Wheel color	Graphite black (RAL9011)
Threadguards	Without threadguard
Diameter	3.15 in
Tread width	1.38 in
Axle hole diameter	0.47 in
Hub length	1.75 in
Body width	1.38 in
Hardness of tread (A)	80 Shore A

PERFORMANCE

Roll Performance	●●●○○
Movement noise	●●●●○
Attrition	●●●○○
Corrosion resistance	●●●○○

CORE ATTRIBUTES

Product name	Puretech
Type	Wheel
Standard	EN12532 - Transport Equipment
Load capacity at 2.5 mph	154.32 lb
Electric conductive	no
Stainless	no
Load capacity Static	308.65 lb
Temperature range (Minimum)	-4 °F
Temperature range (Maximum)	140 °F
Overall weight	0.36 lb

© Copyright 2026 TENTE International GmbH


PURETECH

PVR 080x35-Ø12 HL44,4

EAN 4031582321241

Order number 00004985

Product Drawings



© Copyright 2026 TENTE International GmbH