

ALPHA STAINLESS

8470UOO125P30-11

EAN 4031582370157



BETTER MOBILITY. BETTER LIFE.



Slika se može razlikovati od originalnog proizvoda

PERFORMANSE

Performanse kotrljanja ● ● ● ○ ○

Buka u pokretu ● ● ● ○ ○

Ishrana ● ● ● ● ●

otpornost na rdju ● ● ● ● ●

OSNOVNI ATRIBUTI

Naziv proizvoda	Alpha stainless
Tip kućišta	Okretanje Tocak
Standard	EN12532 - transportna oprema
Nosivost na 4 km/h	150 kg
Statički Nosivost	300 kg
Temperaturni opseg (Minimalno)	-40 °C
Opseg temperature (maksimalni)	80 °C
Sveukupna visina	155 mm
Ukupna težina	0,839 kg

TOCAK

Materijal za telo	poliamid
materijal omotaca	Identično sa telom Tocak
Nošenje	klizni lezaj
osovina	Završena sa navrtkom
stitnici omotaca	Bez stražara
Prečnik	125 mm
Širina omotac	40 mm
Teškoća gazećeg omotac (D)	75 Šor D

KUCISTE

Materijal	nerdjajuci čelik, težak
oblik viljuska	siroko
okretni lezaj	Dve lopte
ofset	40 mm
okretni radijus	102,5 mm
Otpor okretanju	205 mm
nerdjajuci	✓

PRILAGOĐAVANJE

Tip uklapanja	otvor za vijak
dimenzija rupa sraf	11 mm

ALPHA STAINLESS

8470UOO125P30-11

EAN 4031582370157



BETTER MOBILITY. BETTER LIFE.

TEHNIČKI CRTEŽI

