

PRODUCT INFORMATION

BASETECH

POR080x30-Ø12 RAL9011 TFR

EAN 4031582414325



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll Performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ● ●
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Basetech
Type	Wheel
Standard	EN12532 - Transport Equipment
Load capacity at 2.5 mph	220.46 lb
Electric conductive	no
Stainless	no
Load capacity Static	440.92 lb
Temperature range (Minimum)	-4 °F
Temperature range (Maximum)	140 °F
Overall weight	0.13 lb

WHEEL

Body material	Polypropylene
Tread material	Identical with wheel body
Bearing	Roller bearing
Threadguards	Without threadguard
Diameter	3.15 in
Tread width	1.18 in
Axle hole diameter	0.79 in
Hub length	1.73 in
Hardness of tread (D)	65 Shore D

BASETECH

POR080x30-Ø12 RAL9011 TFR

EAN 4031582414325



BETTER MOBILITY. BETTER LIFE.

Product Drawings

