

NOVATECH

ITP 250x50-Ø20 HL60 soft cv

EAN 4031582366273



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

WHEEL


Tread profile	convex
Tread hardness	soft
Body material	Aluminium
Tread Material Mix	Polyurethane, casted
Bearing	Precision ball bearing
Wheel Color	Traffic grey A (RAL7042)
Threadguards	Without threadguard
Diameter	250 mm
Tread width	50 mm
Axle Hole Diameter	20 mm
Hub Length	60 mm
Body width	50 mm
Hardness of tread (A)	80 Shore A

PERFORMANCE

Roll Performance	● ● ● ● ○
Movement Noise	● ● ● ● ○
Attrition	● ● ● ● ○
Corrosion Resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product Name	Novatech
Type	Wheel
Standard	EN12532 - Transport Equipment
Load capacity at 4 km/h	800 kg
Load capacity at 6 km/h	640 kg
Electric Conductive	No
Stainless	No
Load capacity Static	1600 kg
Temperature range (Minimum)	-10 °C
Temperature range (Maximum)	60 °C
Overall weight	2.18 kg




PRODUCT INFORMATION

NOVATECH

ITP 250x50-Ø23, H160, soft cv

EAN 4031582366273

Order number 008351103



BETTER MOBILITY. BETTER LIFE.