

MAXTECH

UAP075X15-Ø8

EAN 4031582464191



BETTER MOBILITY. BETTER LIFE.

PERFORMANCE

| | |
|----------------------|-----------|
| Roll performance | ● ● ● ○ ○ |
| Movement noise | ● ● ● ○ ○ |
| Attrition | ● ● ● ● ○ |
| Corrosion resistance | ● ● ● ○ ○ |

CORE ATTRIBUTES

| | |
|-----------------------------|---------------------------|
| Product name | Maxtech |
| Housing type | Wheel |
| Standard | EN12530 - Devices Castors |
| Load capacity at 3 km/h | 50 kg |
| Load capacity Static | 100 kg |
| Temperature range (Minimum) | -40 °C |
| Temperature range (Maximum) | 80 °C |
| Overall weight | 0.05 kg |

WHEEL

| | |
|-----------------------|------------------------|
| Body material | Polyamide |
| Tread material | Polyurethane, injected |
| Bearing | Precision ball bearing |
| Threadguards | With threadguard |
| Diameter | 75 mm |
| Tread width | 15 mm |
| Axle hole diameter | 8 mm |
| Hub length | 7 mm |
| Hardness of tread (D) | 40 Shore D |

MAXTECH

UAP075X15-Ø8

EAN 4031582464191



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

