

MAXTECH

PAP3.5X1.25-Ø9.8 HL41

EAN 4031582436174



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

WHEEL

Body material	Polypropylene
Tread material	Polyurethane, injected
Bearing	Precision ball bearing
Threadguards	With threadguard
Diameter	3.5 in
Tread width	1.25 in
Axle hole diameter	0.39 in
Hub length	1.61 in
Hardness of tread (D)	41 Shore D

PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ○ ○ ○
Attrition	● ● ● ● ○
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Maxtech
Housing type	Wheel
Standard	Institute of Casters and Wheel Manufacturers
Load capacity at 1.8 mph	249.12 lb
Load capacity Static	498.24 lb

MAXTECH

PAP3.5X1.25-Ø9.8 HL41

EAN 4031582436174



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

